

BD LSRFortessa™ 4 SORP configuration table

Detector	Mirror	Filter	Excitation lasers			
			405nm	488nm	561nm	640nm
FSC	—	—				
SSC	—	488/10 BP				
405-F	—	450/50 BP				
405-E	495 LP	525/50 BP				
405-D	595 LP	610/20 BP				
405-C	635 LP	660/20 BP				
405-B	685 LP	710/50 BP				
405-A	750 LP	780/60 BP	IR			
488-B	505 LP	530/30 BP				
488-A	670 LP	695/40 BP				
561-D	—	586/15 BP				
561-C	595 LP	610/20 BP				
561-B	685 LP	710/50 BP				
561-A	750 LP	780/60 BP			IR	
640-C	—	670/30 BP				
640-B	685 LP	730/45 BP				
640-A	740 LP	780/60 BP				IR